

**B4** 

**B**3

**B2** 

**B1** 

Manifold Control Module

Α4

A3

A2

A1

## **396-2689Y1** LiquiShift Multiple Sections Stainless Steel Manifolds Assembly and Mounting

Feed into the section valve stack using 3/4", 1", or 1-1/2" hose from the pump. Each section valve output hose may be split using tees or crosses to feed the necessary number of manifolds per section.

Valve Stack can mount directly to forward/ backward frame. Use optional bracket kit 515-105100 to mount valve stack to lateral frame members.



If applying dual products, use bracket 515-105200 to raise the second valve stack above the first to allow visibility of the valves.

Metering Tube

Sizes

Orange 0.150

I.D.

0.187

0.170

0.125

0.110

0.096

0.080

0.060

Color

Black

Yellow

Tan

Green Blue

Purple

Grav





## LiquiShift 2 Section Example Setup

Flowmeter Kit	Range	Hose Barb Size
500-02-2050	.3-5 GPM	3/4"
500-02-2060	.6-13 GPM	1"
500-02-2070	1.3-26 GPM	1"
500-02-1080	2.6-53 GPM	1-1/2"





396-2689Y1 LiquiShift Multiple Sections SS Manifolds

Page 3 © 2014-2022 SurePoint Ag Systems, Inc.

Revised: 5/24/2022